



Click [here](#) for the 3D model.

Dimensions

L	57.5mm +0.8/-0.7mm
H	50mm +0.3/-0.7mm
T	35mm +0.5/-0.7mm
S	52.5mm +/-0.4mm
S1	20.3mm +/-0.4mm
LL	6mm -2mm
F	1.2mm +/-0.05mm

Packaging Specifications

Packaging	Bulk, Box
Packaging Quantity	23

General Information

Series	C4AQ-P
Dielectric	Metallized Polypropylene
Style	Radial
Features	DC Filtering
RoHS	Yes
Lead	4 Wire Leads
Qualifications	AEC-Q200, IEC61071, EN61071, VDE0560
AEC-Q200	Yes
Typical Component Weight	134.1g
Miscellaneous	Rth = 10 C/W.

Specifications

Capacitance	27 uF
Capacitance Tolerance	5%
Voltage DC	1100 VDC
Temperature Range	-55/+125°C
Insulation Resistance	1.11 GOhms
Max dV/dt	20 V/us
ESR	5.39 mOhms (10kHz 70C)
Ripple Current	22.8 Amps Irms (10kHz 75C), 540 Amps Ipk
Inductance	15 nH