



Click [here](#) for the 3D model.

Dimensions	
L	41.5mm +1.5/-0.7mm
H	40mm +0.2/-0.7mm
T	20mm +0.4/-0.7mm
S	22mm +/-0.2mm
S1	16mm +/-0.2mm
S2	28mm +/-0.2mm
P	6mm NOM

Packaging Specifications	
Packaging	Bulk, Bag
Packaging Quantity	48

General Information	
Series	C4BS
Dielectric	Metallized Polypropylene
Style	Radial
Features	IGBT Circuit
RoHS	Yes
Lead	Flat Tabs
AEC-Q200	No
Typical Component Weight	61.88 g
Miscellaneous	KEMET Style B Tabs.

Specifications	
Capacitance	0.68 uF
Capacitance Tolerance	5%
Voltage DC	1200 VDC
Voltage AC	630 VAC
Temperature Range	-40/+85°C
Rated Temperature	70°C
Max dV/dt	965 V/us
ESR	4.7 mOhms (100kHz)
Ripple Current	21 Amps (100kHz 70C), 656 Amps (Peak)
Inductance	41 nH