


## C637L103MHR5TA7303

Aliases (C637L103MHR5TATR)
GoldMax 600 Comm X7R HV, Ceramic, 0.01 uF, 20%, 3,000 VDC, X7R, GoldMax, Commercial Standard, 9.53 mm



Click here for the 3D mode	el.
----------------------------	-----

General Information	
Series	GoldMax 600 Comm X7R HV
Style	Radial
Description	GoldMax, Commercial Standard
Features	Commercial
RoHS	With Exemptions
REACH	SVHC (Pb - CAS 7439-92-1)
Termination	Tin
Lead	Formed
Failure Rate	N/A
AEC-Q200	No

Dimensions	
L	7.62mm MAX
Н	7.62mm MAX
Т	5.08mm MAX
S	9.53mm NOM
LL	31mm MIN
F	0.635mm NOM

Packaging Specifications	
Packaging	T&R, 305mm, Type II, H0 = 18mm
Packaging Quantity	250

Specifications	
Capacitance	0.01 uF
Measurement Condition	1 kHz 1.0Vrms
Tolerance	20%
Voltage DC	3000 VDC
Dielectric Withstanding Voltage	3,600 VDC
Temperature Range	-55/+125°C
Temp. Coefficient	X7R
Capacitance Change with Reference to +25°C and 0 VDC Applied (TCC)	0.15, 1kHz 1.0Vrms
Dissipation Factor	2.5%1kHz1.0Vrms
Aging Rate	3% Loss/Decade Hour: Referee Time is 1000 Hours
Insulation Resistance	100 GOhms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 11/22/2025 © 2006 - 2025 YAGEO