


General Information



GoldMax 600 Comm COG HV, Ceramic, 1,000 pF, 10%, 3,000 VDC, COG, GoldMax, Commercial Standard, 9.52 mm



Series	GoldMax 600 Comm COG HV
Style	Radial
Description	GoldMax, Commercial Standard
RoHS	With Exemptions
REACH	SVHC (Pb - CAS 7439-92-1)
Termination	Tin
Lead	Crimped
	Chiliped
Failure Rate	N/A
Failure Rate AEC-Q200	·
. and o Hate	N/A

Click here for the 3D model.

Dimensions	
L	11.9mm MAX
Н	15.74mm MAX
Т	6.89mm MAX
S	9.52mm NOM
LL	7mm MIN
F	0.64mm NOM

Packaging Specifications	
Packaging	Bulk, Bag
Packaging Quantity	50

Specifications	
Capacitance	1,000 pF
Measurement Condition	1 MHz 1.0Vrms
Tolerance	10%
Voltage DC	3000 VDC
Dielectric Withstanding Voltage	3,600 VDC
Temperature Range	-55/+125°C
Temp. Coefficient	COG
Capacitance Change with Reference to +25°C and 0 VDC Applied (TCC)	30PPM/C, 1MHz 1.0Vrms
Dissipation Factor	0.1% 1 MHz 1.0Vrms
Aging Rate	0% Loss/Decade Hour
Insulation Resistance	100 GOhms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 10/21/2025 © 2006 - 2025 YAGEO