


## C917U180JZNDAAWL30

## Obsolete

C900AC SFTY X1-440 Y2-300, Ceramic, 18 pF, 5%, 440 VAC (X1), 300 VAC (Y2), COG, 7.5 mm





The measurement position of Lead Spacing (S) and Width (V) is critical in straight lead capacitors.

General Information	
Series	C900AC SFTY X1-440 Y2-300
Style	Radial Disc
RoHS	Yes
Termination	Tin
Lead	Wire Leads
Failure Rate	N/A
Qualifications	VDE, ENEC, UL, cUL
AEC-Q200	No

Dimensions	
D	8mm MAX
Т	5mm MAX
S	7.5mm +/-1mm
LL	3mm +/-1mm
F	0.5mm +/-0.1mm

Packaging Specifications	
Packaging	Bulk, Bag
Packaging Quantity	500

Specifications	
Capacitance	18 pF
Tolerance	5%
Voltage AC	440 VAC (X1), 300 VAC (Y2)
Temperature Range	-40/+125°C
Temp. Coefficient	COG
Insulation Resistance	10 GOhms
Safety Class	X1/Y2

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 11/04/2025 © 2006 - 2025 YAGEO