



#### General Information

|                |                           |
|----------------|---------------------------|
| Series         | C900AC SFTY X1-400 Y2-250 |
| Style          | Radial Disc               |
| RoHS           | Yes                       |
| Termination    | Tin                       |
| Lead           | Crimped Out               |
| Failure Rate   | N/A                       |
| Qualifications | VDE, ENEC, UL, cUL        |
| AEC-Q200       | No                        |

#### Dimensions

|    |                |
|----|----------------|
| D  | 9mm MAX        |
| T  | 5mm MAX        |
| S  | 10mm +/-1mm    |
| LL | 5mm +/-1mm     |
| F  | 0.5mm +/-0.1mm |

#### Packaging Specifications

|                    |           |
|--------------------|-----------|
| Packaging          | Bulk, Bag |
| Packaging Quantity | 500       |

#### Specifications

|                       |                            |
|-----------------------|----------------------------|
| Capacitance           | 27 pF                      |
| Tolerance             | 5%                         |
| Voltage AC            | 400 VAC (X1), 250 VAC (Y2) |
| Temperature Range     | -40/+125°C                 |
| Temp. Coefficient     | COG                        |
| Insulation Resistance | 10 GOhms                   |
| Safety Class          | X1/Y2                      |