


## CAS17C120FAGFC

## Obsolete

CAS SMD SFTY 250, Ceramic, 12 pF, 1%, 250 VAC, COG, Industrial Grade, Safety MLCC, X1/Y2, 3.5 mm, 1808 / 4520



Click	horo	for the	3D	mode
CIICK	nere	TOT LITE	· SD	mode

General Information	
Series	CAS SMD SFTY 250
Style	SMD Chip
Description	Industrial Grade, Safety MLCC
RoHS	Yes
Termination	Tin
Qualifications	TUV, UL, cUL
AEC-Q200	No
Halogen Free	Yes
Shelf Life	52 Weeks

Dimensions	
L	4.5mm +0.5/-0.3mm
W	2mm +/-0.25mm
Т	1.4mm +/-0.15mm
S	3.5mm MIN
В	0.5mm +/-0.25mm
Case Code (EIA / mm)	1808 / 4520

Packaging Specifications			
Packaging	T&R		
Packaging Quantity	2000		

Specifications	
Capacitance	12 pF
Measurement Condition	1 MHz 1.0Vrms
Tolerance	1%
Voltage AC	250 VAC (X1), 250 VAC (Y2)
Temperature Range	-55/+125°C
Temp. Coefficient	COG
Capacitance Change with Reference to +25°C and 0 VDC Applied (TCC)	30 ppm/C, 1kHz 1.0Vrms
Insulation Resistance	100 GOhms
Quality Factor	640
Safety Class	X1/Y2

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 12/02/2025 © 2006 - 2025 YAGEO