



General Information

Series	C9T
Dielectric	Metallized Polypropylene
Style	Can
Features	Three Phase PFC
RoHS	Yes
Lead	Quick Connect
Qualifications	VDE
AEC-Q200	No
Typical Component Weight	1,208 g
Miscellaneous	3x Rated Capacitance, Delta Connection. Q = 12.5 kvar. Operating Freq. = 50 Hz.
Notes	Not For New Design.

Dimensions

D	75mm +/-0.5mm
L	220mm +/-2mm

Packaging Specifications

Terminal Type	Bolt - M12x16
Packaging	Bulk, Bag
Packaging Quantity	12

Specifications

Capacitance	77 uF
Tolerance	-5/+10%
Voltage AC	415 VAC
Temperature Range	-25/+55°C
Rated Temperature	55°C
Max dV/dt	30 V/us
Ripple Current	17.4 Amps
Irms	17.4 A

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.