



#### General Information

Series	C9T
Dielectric	Metallized Polypropylene
Style	Can
Features	Three Phase PFC
RoHS	Yes
Lead	Quick Connect
Qualifications	VDE
AEC-Q200	No
Miscellaneous	3x Rated Capacitance, Delta Connection. Q = 17.5 kvar. Operating Freq. = 50 Hz.
Notes	Not For New Design.

#### Dimensions

D	75mm +/-0.5mm
L	280mm +/-2mm

#### Packaging Specifications

Terminal Type	Bolt - M12x16
Packaging	Bulk, Bag
Packaging Quantity	12

#### Specifications

Capacitance	67.4 uF
Tolerance	-5/+10%
Voltage AC	525 VAC
Temperature Range	-25/+55°C
Rated Temperature	55°C
Max dV/dt	30 V/us
Ripple Current	19.2 Amps
Irms	19.2 A

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.