




C9T, Film, Metallized Polypropylene, AC Filter, 66.8 uF, -5/+10%, 690 VAC





| General Information | |
|---------------------|---|
| Series | С9Т |
| Dielectric | Metallized Polypropylene |
| Style | Can |
| Features | Three Phase PFC |
| RoHS | Yes |
| Lead | Quick Connect |
| Qualifications | VDE |
| AEC-Q200 | No |
| Miscellaneous | 3x Rated Capacitance, Delta Connection. Q = 30 kvar. Operating Freq. = 50 Hz. |
| Notes | Not For New Design. |

| Dimensions | |
|--------------------------|----------------------------|
| D | 95mm +/-0.5mm |
| L | 280mm +/-2mm |
| | |
| Packaging Specifications | |
| Terminal Type | |
| теттіна туре | Bolt - M12x16 |
| Packaging | Bolt - M12x16 Bulk, Bag |

| Specifications | |
|-------------------|-----------|
| Capacitance | 66.8 uF |
| Tolerance | -5/+10% |
| Voltage AC | 690 VAC |
| Temperature Range | -25/+55°C |
| Rated Temperature | 55°C |
| Max dV/dt | 30 V/us |
| Ripple Current | 25.1 Amps |
| Irms | 25.1 A |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 10/25/2025 © 2006 - 2025 YAGEO