




CAS SMD SFTY 250, Ceramic, 1,500 pF, 10%, 250 VAC, X7R, Industrial Grade, Safety MLCC, X1/Y2, 4 mm, 2220 / 5651



Click	horo	for the	3D	model.
CIICK	nere	TOT LITE	- 20	model

General Information	
Series	CAS SMD SFTY 250
Style	SMD Chip
Description	Industrial Grade, Safety MLCC
RoHS	Yes
Termination	Tin
Qualifications	TUV, UL, cUL
AEC-Q200	No
Halogen Free	Yes
Shelf Life	52 Weeks

Dimensions		
L	5.7mm +/-0.4mm	
W	5mm +/-0.4mm	
Т	2.5mm +/-0.3mm	
S	4mm MIN	
В	0.6mm +/-0.3mm	
Case Code (EIA / mm)	2220 / 5651	

Packaging Specifications		
Packaging	T&R	
Packaging Quantity	500	

Specifications	
Capacitance	1,500 pF
Measurement Condition	1 kHz 1.0Vrms
Tolerance	10%
Voltage AC	250 VAC (X1), 250 VAC (Y2)
Temperature Range	-55/+125°C
Temp. Coefficient	X7R
Capacitance Change with Reference to +25°C and 0 VDC Applied (TCC)	15%, 1kHz 1.0Vrms
Dissipation Factor	2.5% 1 kHz 1.0Vrms
Insulation Resistance	10 GOhms
Safety Class	X1/Y2

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 12/08/2025 © 2006 - 2025 YAGEO