



Click [here](#) for the 3D model.

General Information

Series	CAS SMD SFTY 250
Style	SMD Chip
Description	Industrial Grade, Safety MLCC
RoHS	Yes
Termination	Tin
Qualifications	TUV, UL, cUL
AEC-Q200	No
Halogen Free	Yes
Shelf Life	52 Weeks

Dimensions

Chip Size	1808
L	4.5mm +0.5/-0.3mm
W	2mm +/-0.25mm
T	1.6mm +/-0.2mm
S	3.5mm MIN
B	0.5mm +/-0.25mm

Packaging Specifications

Packaging	T&R
Packaging Quantity	2000

Specifications

Capacitance	330 pF
Measurement Condition	1 kHz 1.0Vrms
Tolerance	20%
Voltage AC	250 VAC (X2)
Temperature Range	-55/+125°C
Temp. Coefficient	X7R
Capacitance Change with Reference to +25°C and 0 VDC Applied (TCC)	15%, 1kHz 1.0Vrms
Dissipation Factor	2.5%
Insulation Resistance	10 GOhms
Safety Class	X2

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.