


CKC33C883KJGLCTU

Aliases (CKC33C883KJGLC7800)

KONNEKT KC-LINK Comm COG, Ceramic, 0.088 uF, 10%, 1,700 VDC, COG, 4-Chip Standard Orientation.



Click	here	for	the	ЗD	model	ı
CIICK	Hele	101	uie	$^{\circ}$	model	ı.

Dimensions	
L	9.3mm +/-0.6mm
W	10.2mm +/-0.4mm
T	10.3mm +/-0.8mm
В	1.27mm +/-0.4mm

Packaging Specifications		
Packaging	T&R, 180mm	
Packaging Quantity	50	

General Information	
Series	KONNEKT KC-LINK Comm COG
Style	KONNEKT
Description	KC-LINK with KONNEKT, SMD, MLCC, Ultra-Stable, Class I
Features	Ultra-Stable
RoHS	Yes
Termination	Tin
AEC-Q200	No
Typical Component Weight	4.3 g
Notes	4-Chip Standard Orientation.
Chip Size	3640-4
MSL	1

Specifications	
Capacitance	0.088 uF
Measurement Condition	1 kHz 1.0Vrms
Tolerance	10%
Voltage DC	1700 VDC
Dielectric Withstanding Voltage	2,040 VDC
Temperature Range	-55/+150°C
Temp. Coefficient	COG
Capacitance Change with Reference to +25°C and 0 VDC Applied (TCC)	30 ppm/C, 1kHz 1.0Vrms
Dissipation Factor	0.1% 1 kHz 1.0Vrms
Aging Rate	0% Loss/Decade Hour
Insulation Resistance	11.3636 GOhms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 10/25/2025 © 2006 - 2025 YAGEO