
EA2-24TNU

KEMET, EA2, Relays, Signal





General Information	
Series	EA2
Style	Through-Hole
Description	Miniature Signal Relay, Double Coil Latch
Features	Compact Size, Flat-Package. FCC (1500 V) surge capacity. UL recognized and CSA certified. Low power consumption (100-200 mW)
RoHS	Yes
Coil Type	Double Coil (Latching)

Click here for the 3D model.

Dimensions	
Н	5.4mm MAX
L	14.2mm MAX
W	9.2mm MAX
LL	3.5mm +/-0.2mm
S	7.62mm +/-0.2mm
S1	2.54mm +/-0.2mm
F	0.5mm +/-0.2mm
F1	0.25mm +/-0.1mm

Packaging Specifications		
Packaging	Bulk	

Specifications	
Temperature Range	-40/+85°C
Coil Voltage	24 V
Contact Form	2 Form C (DPDT)
Switching Current	1A
Coil Resistance	2880 Ohms +/-10%
Contact Material	Silver alloy with gold alloy overlay
Voltage Characteristics	18 (Set/Reset)
Power	200 mW
Switching Power	30 W, 62.5 VA
Switching Voltage DC	220 V
Switching Voltage AC	250 VAC
Contact Current Class	>10A
Carrying Current	2 Amps
Contact Resistance	75 mOhms
Operation Time	Approximately 2ms
Release Time	Approximately 1ms
Insulation Resistance	1GOhms
Withstanding Voltage	1000 VAC (1min) 1500 V Surge

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 10/16/2025 © 2006 - 2025 YAGEO