



Click [here](#) for the 3D model.

#### General Information

|             |                                      |
|-------------|--------------------------------------|
| Series      | EDH                                  |
| Dielectric  | Aluminum Electrolytic                |
| Style       | SMD Can                              |
| Description | Surface Mount, Aluminum Electrolytic |
| RoHS        | Yes                                  |
| Lead        | V-Chip                               |
| AEC-Q200    | No                                   |

#### Dimensions

|   |                |
|---|----------------|
| D | 16mm +/-0.5mm  |
| L | 16.5mm +/-1mm  |
| W | 2mm +/-0.2mm   |
| F | 0.3mm MAX      |
| A | 17mm +/-0.2mm  |
| B | 17mm +/-0.2mm  |
| C | 18.7mm MAX     |
| E | 5.8mm +/-0.2mm |
| G | 1mm +/-0.2mm   |
| P | 6mm +/-0.2mm   |

#### Packaging Specifications

|           |     |
|-----------|-----|
| Packaging | T&R |
|-----------|-----|

#### Specifications

|                                 |                        |
|---------------------------------|------------------------|
| Capacitance                     | 1,000 uF               |
| Tolerance                       | 20%                    |
| Voltage DC                      | 50 VDC, 63 VDC (Surge) |
| Temperature Range               | -40/+105°C             |
| Rated Temperature               | 105°C                  |
| Life                            | 2000 Hrs               |
| Dissipation Factor              | 18% 120Hz 20C          |
| Ripple Current                  | 800 mAmps (120Hz 105C) |
| Compare Ripple Current at 120Hz | 0.8                    |
| High Temperature Solder         | Yes                    |
| Leakage Current                 | 500 uA (2min 20°C)     |
| Impedance Ratio at -25C         | 2                      |
| Impedance Ratio at -40C         | 3                      |