



Click [here](#) for the 3D model.

General Information

Series	EDT
Dielectric	Aluminum Electrolytic
Style	SMD Can
Description	Surface Mount, Aluminum Electrolytic
RoHS	Yes
Lead	V-Chip
AEC-Q200	No

Specifications

Capacitance	100 uF
Tolerance	20%
Voltage DC	10 VDC, 13 VDC (Surge)
Temperature Range	-40/+125°C
Rated Temperature	125°C
Life	1000 Hrs
Dissipation Factor	26%
Ripple Current	75 mAmps (120Hz 125C)
High Temperature Solder	Yes
Leakage Current	10 uA (2min 20°C)
Impedance Ratio at -25C	2
Impedance Ratio at -40C	3

Dimensions

D	8mm +/-0.5mm
L	6.2mm +/-0.3mm
W	0.65mm +/-0.1mm
F	0.3mm MAX
A	8.3mm +/-0.2mm
B	8.3mm +/-0.2mm
C	9.5mm MAX
E	3.3mm +/-0.2mm
G	0.35mm +0.15/-0.2mm
P	2.2mm +/-0.2mm

Packaging Specifications

Packaging	T&R
-----------	-----