



Click [here](#) for the 3D model.

#### General Information

Series	ELD
Dielectric	Aluminum Electrolytic
Description	Snap-In, Aluminum Electrolytic
RoHS	Yes
Lead	2 Pin
AEC-Q200	No

#### Specifications

Capacitance	180 uF
Tolerance	20%
Voltage DC	400 VDC, 450 VDC (Surge)
Temperature Range	-25/+105°C
Rated Temperature	105°C
Life	3000 Hrs
Dissipation Factor	15% 120Hz 20C
ESR	1.105 Ohms (120Hz 20C)
Ripple Current	1.14 Amps (120Hz 105C)
Leakage Current	1.44 mA (5min 20°C)

#### Dimensions

D	22mm +1.0mm
L	50mm +2.0mm
S	10mm +/-0.5mm
LL	5.8mm +/-1mm
F	1.5mm +/-0.1mm

#### Packaging Specifications

Packaging	Bulk, Bag
Packaging Quantity	400