



Click [here](#) for the 3D model.

General Information

| | |
|-------------|--------------------------------|
| Series | ELH |
| Dielectric | Aluminum Electrolytic |
| Description | Snap-In, Aluminum Electrolytic |
| RoHS | Yes |
| Lead | 2 Pin |
| AEC-Q200 | No |

Specifications

| | |
|--------------------|-------------------------|
| Capacitance | 6,800 uF |
| Tolerance | 20% |
| Voltage DC | 35 VDC, 44 VDC (Surge) |
| Temperature Range | -40/+85°C |
| Rated Temperature | 85°C |
| Life | 2000 Hrs |
| Dissipation Factor | 35% 120Hz 20C |
| ESR | 0.0683 Ohms (120Hz 20C) |
| Ripple Current | 2.9 Amps (120Hz 85C) |
| Leakage Current | 3 mA (5min 20°C) |

Dimensions

| | |
|----|----------------|
| D | 30mm +1mm |
| L | 25mm +2mm |
| S | 10mm +/-0.5mm |
| LL | 5.8mm +/-1mm |
| F | 1.5mm +/-0.1mm |

Packaging Specifications

| | |
|--------------------|-----------|
| Packaging | Bulk, Bag |
| Packaging Quantity | 200 |