
EDH335M400A9RAA







| General Information | |
|---------------------|---|
| Series | EDH |
| Dielectric | Aluminum Electrolytic |
| Style | SMD Can |
| Description | Surface Mount, Aluminum Electrolytic |
| RoHS | Yes |
| Lead | V-Chip |
| AEC-Q200 | No |

Click here for the 3D model.

| Dimensions | |
|--------------------------|-----------------|
| D | 12.5mm +/-0.5mm |
| L | 13.5mm +/-1mm |
| W | 1.2mm +/-0.2mm |
| F | 0.3mm MAX |
| A | 13mm +/-0.2mm |
| В | 13mm +/-0.2mm |
| С | 15mm MAX |
| E | 4.8mm +/-0.2mm |
| G | 0.7mm +/-0.3mm |
| P | 4.4mm +/-0.2mm |
| | |
| Packaging Specifications | |

T&R

Packaging

| Specifications | |
|---------------------------------|--------------------------|
| Capacitance | 3.3 uF |
| Tolerance | 20% |
| Voltage DC | 400 VDC, 450 VDC (Surge) |
| Temperature Range | -25/+105°C |
| Rated Temperature | 105°C |
| Life | 2000 Hrs |
| Dissipation Factor | 25% 120Hz 20C |
| Ripple Current | 40 mAmps (120Hz 105C) |
| Compare Ripple Current at 120Hz | 0.04 |
| High Temperature Solder | Yes |
| Leakage Current | 152.8 uA (2min 20°C) |
| Impedance Ratio at -25C | 4 |

| Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and | |
|--|--|
| we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the | |
| requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us | |
| with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained. | |

Generated 10/28/2025 © 2006 - 2025 YAGEO