



Click [here](#) for the 3D model.

General Information

Series	EDH
Dielectric	Aluminum Electrolytic
Style	SMD Can
Description	Surface Mount, Aluminum Electrolytic
RoHS	Yes
Lead	V-Chip
AEC-Q200	No

Specifications

Capacitance	33 uF
Tolerance	20%
Voltage DC	100 VDC, 125 VDC (Surge)
Temperature Range	-40/+105°C
Rated Temperature	105°C
Life	2000 Hrs
Dissipation Factor	18% 120Hz 20C
Ripple Current	120 mAmps (120Hz 105C)
Compare Ripple Current at 120Hz	0.12
High Temperature Solder	Yes
Leakage Current	33 uA (2min 20°C)
Impedance Ratio at -25C	2
Impedance Ratio at -40C	3

Dimensions

D	8mm +/-0.5mm
L	10.2mm +/-0.3mm
W	0.9mm +/-0.2mm
F	0.3mm MAX
A	8.3mm +/-0.2mm
B	8.3mm +/-0.2mm
C	10mm MAX
E	2.9mm +/-0.2mm
G	0.7mm +/-0.2mm
P	3.1mm +/-0.2mm

Packaging Specifications

Packaging	T&R
-----------	-----