
## EDT107M010S9LAA

EDT, Aluminum, Aluminum Electrolytic, 100 uF, 20%, 10 VDC, -40/+125°C





| General Information |   |
|---------------------|---|
| Series              | EDT                                     |
| Dielectric          | Aluminum Electrolytic                   |
| Style               | SMD Can                                 |
| Description         | Surface Mount, Aluminum<br>Electrolytic |
| RoHS                | Yes                                     |
| Lead                | V-Chip                                  |
| Qualifications      | AEC-Q200                                |
| AEC-Q200            | Yes                                     |

Click here for the 3D model.

| Dimensions |                     |
|------------|---------------------|
| D          | 8mm +/-0.5mm        |
| L          | 6.2mm +/-0.3mm      |
| W          | 0.65mm +/-0.1mm     |
| F          | 0.3mm MAX           |
| A          | 8.3mm +/-0.2mm      |
| В          | 8.3mm +/-0.2mm      |
| С          | 9.5mm MAX           |
| E          | 3.3mm +/-0.2mm      |
| G          | 0.35mm +0.15/-0.2mm |
| P          | 2.2mm +/-0.2mm      |
|            |                     |

| P                        | 2.2mm +/-0.2mm |
|--------------------------|----------------|
| Packaging Specifications |                |
| Packaging                | T&R            |

| Specifications          |                        |
|-------------------------|------------------------|
| Capacitance             | 100 uF                 |
| Tolerance               | 20%                    |
| Voltage DC              | 10 VDC, 13 VDC (Surge) |
| Temperature Range       | -40/+125°C             |
| Rated Temperature       | 125°C                  |
| Life                    | 1000 Hrs               |
| Dissipation Factor      | 26%                    |
| Ripple Current          | 75 mAmps (120Hz 125C)  |
| High Temperature Solder | Yes                    |
| Leakage Current         | 10 uA (2min 20°C)      |
| Impedance Ratio at -25C | 2                      |
| Impedance Ratio at -40C | 3                      |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 10/29/2025 © 2006 - 2025 YAGEO