


[Click here](#) for the 3D model.

General Information

Series	EDT
Dielectric	Aluminum Electrolytic
Style	SMD Can
Description	Surface Mount, Aluminum Electrolytic
RoHS	Yes
Lead	V-Chip
Qualifications	AEC-Q200
AEC-Q200	Yes

Dimensions

D	8mm +/-0.5mm	Capacitance	330 uF
L	10.2mm +/-0.3mm	Tolerance	20%
W	0.9mm +/-0.2mm	Voltage DC	10 VDC, 13 VDC (Surge)
F	0.3mm MAX	Temperature Range	-40/+125°C
A	8.3mm +/-0.2mm	Rated Temperature	125°C
B	8.3mm +/-0.2mm	Life	2000 Hrs
C	10mm MAX	Dissipation Factor	26%
E	2.9mm +/-0.2mm	Ripple Current	130 mAmps (120Hz 125C)
G	0.7mm +/-0.2mm	High Temperature Solder	Yes
P	3.1mm +/-0.2mm	Leakage Current	33 uA (2min 20°C)
Packaging Specifications		Impedance Ratio at -25C	2
Packaging		Impedance Ratio at -40C	3

T&R

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.