



Click [here](#) for the 3D model.

General Information

| | |
|-------------|--------------------------------|
| Series | ELG |
| Dielectric | Aluminum Electrolytic |
| Description | Snap-In, Aluminum Electrolytic |
| RoHS | Yes |
| Lead | 2 Pin |
| AEC-Q200 | No |

Specifications

| | |
|-------------------------|--------------------------|
| Capacitance | 150 uF |
| Tolerance | 20% |
| Voltage DC | 450 VDC, 500 VDC (Surge) |
| Temperature Range | -25/+105°C |
| Rated Temperature | 105°C |
| Life | 2000 Hrs |
| Dissipation Factor | 20% 120Hz 20C |
| ESR | 1.769 Ohms (120Hz 20C) |
| Ripple Current | 0.75 Amps (120Hz 105C) |
| Leakage Current | 1.3 mA (5min 20°C) |
| Impedance Ratio at -25C | 8 |

| Dimensions | |
|--------------------------|----------------|
| D | 30mm +1mm |
| L | 30mm +2mm |
| S | 10mm +/-0.5mm |
| LL | 5.8mm +/-1mm |
| F | 1.5mm +/-0.1mm |
| Packaging Specifications | |
| Packaging | Bulk, Bag |
| Packaging Quantity | 200 |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.