



Click [here](#) for the 3D model.

General Information

Series	ELG
Dielectric	Aluminum Electrolytic
Description	Snap-In, Aluminum Electrolytic
RoHS	Yes
Lead	2 Pin
AEC-Q200	No

Specifications

Capacitance	680 uF
Tolerance	20%
Voltage DC	450 VDC, 500 VDC (Surge)
Temperature Range	-25/+105°C
Rated Temperature	105°C
Life	2000 Hrs
Ripple Current	2.1 Amps (120Hz 105C)
Leakage Current	3000 uA (5min 20°C)

Dimensions

D	35mm +1mm
L	60mm +2mm
S	10mm +/-0.5mm
LL	4mm +/-1mm
F	1.5mm +/-0.1mm

Packaging Specifications

Packaging	Bulk, Bag
-----------	-----------