



The measurement position of Lead Spacing (S) and Width (V) is critical in straight lead capacitors.

Click [here](#) for the 3D model.

General Information

| | |
|----------------|---------------------------|
| Series | ERP610 SFTY X1-760 Y1-500 |
| Style | Radial Disc |
| RoHS | Yes |
| Termination | Tin |
| Lead | V-Crimp |
| Qualifications | UL, CSA, CAN, ENEC, VDE |
| AEC-Q200 | No |

Specifications

| | |
|-----------------------|----------------------------|
| Capacitance | 47 pF |
| Tolerance | 10% |
| Voltage AC | 760 VAC (X1), 500 VAC (Y1) |
| Temperature Range | -40/+125°C |
| Temp. Coefficient | Y5S |
| Dissipation Factor | 2.5% |
| Insulation Resistance | 10 GOhms |
| Safety Class | X1/Y1 |

Dimensions

| | |
|----|-----------------|
| D | 8mm MAX |
| T | 6mm MAX |
| S | 10mm NOM |
| LL | 2.8mm +1.5mm |
| F | 0.6mm +/-0.05mm |
| V | 2.3mm +/-0.5mm |

Packaging Specifications

| | |
|-----------|-----------|
| Packaging | Bulk, Bag |
|-----------|-----------|