


ESD-R-38M-H

Aliases (UECESDR38MH000)

EMI Suppression, KEMET, ESD-R-H, Round - Toroidal, Noise Suppression





	Click here for the 3D model.	Toroidal
		Materials
		Core
Dimensions		Specifications
Dimensions D	42mm MAX	Specifications Temperature Range
	42mm MAX 16.7mm +/-1.0mm	

17mm MAX

Packaging Specifications				
Packaging	Tray, Box			
Packaging Quantity	200			
Typical Component Weight	56 g			

Т

General Information	
Series	ESD-R-H
Style	Round - Toroidal
Cable Type	Round Cable
Description	EMI Core Solid, For Round Cables, Toroidal Cores
Features	High Heat Resistance, Cable Holding Mechanism
RoHS	Yes
Qualifications	UL94V-0
AEC-Q200	No
Case Color	White
Toroidal	ESD-R-38D
Materials	Mn-Zn
Core	Mn-Zn Ferrite

Specifications		
Temperature Range	-40/+120°C	
Effective Frequency	10 MHz (AM Band Range)	

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 12/13/2025 © 2006 - 2025 YAGEO