





ESC, Aluminum, Aluminum Electrolytic, 10 uF, 20%, 35 VDC, $-40/+105^{\circ}$ C, 2 mm



TERMINAL END VIEW



Click here for the 3D model.

General Information	
Series	ESC
Dielectric	Aluminum Electrolytic
Description	LowESR Single Ended Aluminum Electrolytic
Features	Low ESR
RoHS	Yes
Lead	Wire Leads
AEC-Q200	No

Dimensions	
D	5mm +/-0.5mm
L	11mm +1.5mm
S	2mm +/-0.5mm
LL Negative	15mm MIN
LL Positive	20mm MIN
F	0.5mm NOM

Packaging Specifications	
Packaging	Bulk, Bag

10 uF
20%
35 VDC, 44 VDC (Surge)
-40/+105°C
105°C
2000 Hrs
12%
0.9 Ohms (100kHz 20C)
140 mAmps (100kHz 105C)
3.5 uA (2min 20°C)
3
4

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 11/04/2025 © 2006 - 2025 YAGEO