





ESH, Aluminum, Aluminum Electrolytic, 4.7 uF, 20%, 500 VDC, -25/ +105°C, 5 mm



General InformationSeriesESHDielectricAluminum ElectrolyticDescriptionHigh CV Single Ended Aluminum ElectrolyticRoHSYesLeadWire LeadsAEC-Q200No

TERMINAL END VIEW



Click here for the 3D model.

Dimensions	
D	10mm +/-0.5mm
L	12.5mm +1.5/-0mm
S	5mm +/-0.5mm
LL Negative	15mm MIN
LL Positive	20mm MIN
F	0.6mm NOM

Packaging Specifications	
Packaging	Bulk, Bag

Specifications	
Capacitance	4.7 uF
Tolerance	20%
Voltage DC	500 VDC, 550 VDC (Surge)
Temperature Range	-25/+105°C
Rated Temperature	105°C
Life	2000 Hrs
Dissipation Factor	25% 120Hz 25C
Ripple Current	38 mAmps (120Hz 105C)
Leakage Current	194 uA (2min 20°C)
Impedance Ratio at -25C	6

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 10/19/2025 © 2006 - 2025 YAGEO