

ESK476M200AL3EA

ESK, Aluminum, Aluminum Electrolytic, 47 uF, 20%, 200 VDC, -25/+85°C, 5 mm



Click [here](#) for the 3D model.

General Information

| | |
|-------------|-------------------------------------|
| Series | ESK |
| Dielectric | Aluminum Electrolytic |
| Description | Single Ended, Aluminum Electrolytic |
| RoHS | Yes |
| Lead | Wire Leads |
| AEC-Q200 | No |

Dimensions

| | |
|-------------|------------------|
| D | 13mm +/-0.5mm |
| L | 20mm +2mm |
| S | 5mm +/-0.5mm |
| LL Negative | 15mm MIN |
| LL Positive | 20mm MIN |
| H0 | 18.5mm +/-0.75mm |
| F | 0.6mm NOM |

Packaging Specifications

| | |
|-----------|------|
| Packaging | Ammo |
|-----------|------|

Specifications

| | |
|-------------------------|--------------------------|
| Capacitance | 47 uF |
| Tolerance | 20% |
| Voltage DC | 200 VDC, 250 VDC (Surge) |
| Temperature Range | -25/+85°C |
| Rated Temperature | 85°C |
| Life | 2000 Hrs |
| Dissipation Factor | 20% 120Hz 20C |
| Ripple Current | 200 mAmps (120Hz 85C) |
| Leakage Current | 292 uA (2min 20°C) |
| Impedance Ratio at -25C | 7 |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.