





ESY, Aluminum, Aluminum Electrolytic, 820 uF, 20%, 63 VDC, -40/+105°C,



TERMINAL END VIEW



Click here for the 3D model.

| General Information |  |
|---------------------|--|
| Series              | ESY  |
| Dielectric          | Aluminum Electrolytic                      |
| Description         | LowZ Single Ended Aluminum<br>Electrolytic |
| RoHS                | Yes  |
| Lead                | Wire Leads                                 |
| AEC-Q200            | No   |

820 uF

20%

3

| Dimensions               |                  |  |  |
|--------------------------|------------------|--|--|
| D                        | 18mm +/-0.5mm    |  |  |
| L                        | 25mm +2mm        |  |  |
| S                        | 7.5mm +/-0.5mm   |  |  |
| LL Negative              | 15mm MIN         |  |  |
| LL Positive              | 20mm MIN         |  |  |
| НО                       | 18.5mm +/-0.75mm |  |  |
| F                        | 0.8mm NOM        |  |  |
|                          |                  |  |  |
| Packaging Specifications |                  |  |  |

Packaging

|              | 7.5mm +/-0.5mm   | Voltage DC              | 63 VDC, 79 VDC (Surge)   |
|--------------|------------------|-------------------------|--------------------------|
|              | 15mm MIN         | Temperature Range       | -40/+105°C               |
|              | 20mm MIN         | Rated Temperature       | 105°C                    |
|              | 18.5mm +/-0.75mm | Life                    | 5000 Hrs                 |
|              | 0.8mm NOM        | Dissipation Factor      | 9% 120Hz 20C             |
|              |                  | ESR                     | 0.042 Ohms (100kHz 20C)  |
| ecifications |                  | Ripple Current          | 2224 mAmps (100kHz 105C) |
| Ammo         | Ammo             | Leakage Current         | 516.6 uA (2min 20°C)     |
|              |                  | Impedance Ratio at -25C | 2                        |

Impedance Ratio at -40C

**Specifications** 

Capacitance

Tolerance

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 10/29/2025 © 2006 - 2025 YAGEO