


**General Information** 

AEC-Q200



ETG, Aluminum, Aluminum Electrolytic, 680 uF, 20%, 35 VDC, -40/+105°C, 3.5 mm



Series ETG

Dielectric Aluminum Electrolytic


Description Single Ended, Aluminum Electrolytic

RoHS Yes

Lead Wire Leads

No

## TERMINAL END VIEW



Click here for the 3D model.

Dimensions	
D	8mm +/-0.5mm
L	30mm +2mm
S	3.5mm +/-0.5mm
LL Negative	15mm MIN
LL Positive	20mm MIN
F	0.6mm NOM

Packaging Specifications	
Packaging	Bulk, Bag

Specifications	
Capacitance	680 uF
Tolerance	20%
Voltage DC	35 VDC, 44 VDC (Surge)
Temperature Range	-40/+105°C
Rated Temperature	105°C
Life	5000 Hrs
Dissipation Factor	12% 120Hz 20C
ESR	0.045 Ohms (100kHz 20C)
Ripple Current	1340 mAmps (100kHz 105C)
Leakage Current	491 uA (2min 20°C)
Impedance Ratio at -25C	2

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 10/29/2025 © 2006 - 2025 YAGEO