


## F462AK103J1K0L

Not for New Design F462, Film, Metallized Polypropylene, General Purpose, 0.01 uF, 5%, 1,000 VDC, 85°C, 10 mm





Click here for the 3D model.

| General Information      |   |
|--------------------------|---|
| Series                   | F462  |
| Dielectric               | Metallized Polypropylene  |
| Style                    | Radial  |
| Features                 | MKP, Pulse  |
| RoHS                     | Yes   |
| Termination              | Tinned Wire   |
| Lead                     | Wire Leads  |
| AEC-Q200                 | No  |
| Typical Component Weight | 1.751 g   |
| Miscellaneous            | The Rated Voltage Decreases 2%/C Between +85C And +105C (1.25%/C For AC). ClimCat: 55/105/56. |
| Notes                    | Series Replaced by R75.   |

| Dimensions               |                  |
|--------------------------|------------------|
| L                        | 13mm -0.5mm      |
| Н                        | 11mm -0.5mm      |
| Т                        | 5mm -0.5mm       |
| S                        | 10mm +0.6/-0.1mm |
| НО                       | 18.5mm +/-0.5mm  |
| F                        | 0.6mm +/-0.05mm  |
| G                        | 0.5mm NOM        |
|                          |                  |
| Packaging Specifications |                  |

| Packaging Specifications |     |
|--------------------------|-----|
| Packaging                | T&R |
| Packaging Quantity       | 600 |

| Specifications        |  |
|-----------------------|--|
| Capacitance           | 0.01 uF                                  |
| Tolerance             | 5%                                       |
| Voltage DC            | 1000 VDC, 600 VDC (105C)                 |
| Voltage AC            | 300 VAC                                  |
| Temperature Range     | -55/+105°C                               |
| Rated Temperature     | 85°C                                     |
| Dissipation Factor    | 0.04% 1kHz, 0.06% 10kHz, 0.25%<br>100kHz |
| Insulation Resistance | 100 GOhms                                |
| Max dV/dt             | 2,000 V/us                               |
| Inductance            | 6 nH                                     |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 10/16/2025 © 2006 - 2025 YAGEO