



General Information

Series	FF1
Style	Sheet
Description	Flex Suppressor Flame Retardant Type
Features	Flame Retardant Type
RoHS	Yes
Qualifications	UL94 V-0, UL File No.E176124, AEC-Q200
Environment	RoHS Compliant, Halogen Free, PVC Free, Lead Free

Specifications

Temperature Range	-40/+125°C
Permeability	100 u At 3MHz
Effective Frequency	1 MHz to 3GHz
Specific Gravity	3.1 TYP
Thermal Conductivity	1.36 typical
Surface Resistivity	1 MOhm/sq. TYP

Dimensions

Sheet Size	240mmx50M
L	50000mm NOM
W	240mm NOM
T	0.1mm NOM

Packaging Specifications

Tape Description	Without PET Tape (Txx00)
Tape Thickness	0.03mm
Typical Component Weight	3902.4 g