


[Click here](#) for the 3D model.

General Information

Series	FLLD4-TH
Style	Chassis Mount
Description	EMI Filter, Chassis Mount, Compact
Features	High Performance
Phase	Three-phase + Neutral
RoHS	Yes
Qualifications	IEC/EN 60939
Terminal Type	Terminal Block

Dimensions

L	230mm NOM
W	135mm NOM
H	125mm NOM
L1	120mm NOM
W1	147.5mm NOM
W2	165mm NOM
J	35mm NOM
K	6.5mm NOM
M (Earth)	Threaded Studs M10

Specifications

Voltage AC	530 VAC
Rated Frequency	50-60 Hz
Rated Current	80 A (50°C)
Ripple Current	80 A (50°C)
Rated Temperature	50°C
Temperature Range	-25/+100°C
Climate Category	25/100/21
Test Voltage DC (P to P)	2250 VDC
Test Voltage DC (P to E)	3000 VDC
Max Power Loss	20 W (25°C 50 Hz)
Leakage Current	11 mA

Packaging Specifications

Packaging	Bulk
Packaging Quantity	1
Typical Component Weight	4,000 g

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.