



Click [here](#) for the 3D model.

#### General Information

Series	FMD
Style	Radial Molded
Description	Radial Molded Double Layer Capacitor
RoHS	Yes
Lead	Wire Leads
Qualifications	AEC-Q200
AEC-Q200	Yes
Typical Component Weight	3.8 g
Miscellaneous	DischargeValue = 0.33 F.

#### Specifications

Capacitance	0.33 F
Tolerance	-20/+80%
Voltage DC	5.5 VDC
Temperature Range	-40/+85°C
Rated Temperature	85°C
ESR	25 Ohms (1kHz)
Current (at 30 minutes after charging)	0.5 mAmps

#### Dimensions

W	14mm +/-0.5mm
H	15mm +/-0.5mm
T	9mm +/-0.5mm
S	5mm +/-0.5mm
LL	5mm +/-1mm
G	0.4mm +/-0.1mm
LT1	0.6mm +/-0.1mm
LT2	0.6mm +/-0.1mm

#### Packaging Specifications

Packaging	Bulk, Bag
Packaging Quantity	400