



General Information

| | |
|---------------|--|
| Series | JSP |
| Dielectric | Metallized Polyester Stacked |
| Style | Radial |
| Features | DC Multipurpose Applications |
| RoHS | Yes |
| Termination | Tinned Wire |
| Lead | Wire Leads |
| Miscellaneous | This Part Number Has One Or More Features That Make It Nonstandard, Semi-Standard, Or Unusual Even Though It May Be A Catalog Part Number. Such Part Numbers Are Often Subject To Long Lead Times. Please Contact KEMET For Details. maxKO = 1890. |

Dimensions

| | |
|----|-----------------|
| L | 41.5mm +0.3mm |
| H | 40mm +0.1mm |
| T | 20mm +0.3mm |
| S | 37.5mm +/-0.4mm |
| LL | 4mm +2mm |
| F | 1mm +/-0.05mm |

Packaging Specifications

| | |
|--------------------|-----------|
| Packaging | Bulk, Bag |
| Packaging Quantity | 126 |

Specifications

| | |
|-----------------------|-------------------------|
| Capacitance | 220 uF |
| Tolerance | 10% |
| Voltage DC | 63 VDC, 35.4 VDC (125C) |
| Voltage AC | 40 VAC |
| Temperature Range | -55/+125°C |
| Rated Temperature | 85°C |
| Dissipation Factor | 1% 1kHz |
| Insulation Resistance | 5.7 MOhms |
| Max dV/dt | 15 V/us |
| Inductance | 22 nH |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.