


## FLLE2150APVT7

Aliases (LLE2150APVT7)

Obsolete

EMI Filters, KEMET, FLLE2-PV, Chassis Mount, Noise Suppression, 220x140x115mm



Click [here](#) for the 3D model.

### General Information

|                |                                         |
|----------------|-----------------------------------------|
| Series         | FLLE2-PV                                |
| Style          | Chassis Mount                           |
| Description    | EMI Filter, With Y Capacitor            |
| Features       | Single Phase, Photovoltaic Applications |
| Phase          | Single-phase                            |
| RoHS           | Yes                                     |
| Qualifications | IEC/EN 60939, UL 1283                   |
| AEC-Q200       | No                                      |
| Lead           | Threaded Studs M10                      |
| Terminal Type  | Threaded Studs M10                      |

### Specifications

|                          |                   |
|--------------------------|-------------------|
| Voltage DC               | 1200 VDC          |
| Rated Current            | 150 A (50°C)      |
| Ripple Current           | 150 A (50°C)      |
| Rated Temperature        | 55°C              |
| Temperature Range        | -40/+100°C        |
| Climate Category         | 40/100/21         |
| Test Voltage DC (P to P) | 1300 VDC          |
| Test Voltage DC (P to E) | 1300 VDC          |
| Max Power Loss           | 20 W (25°C 50 Hz) |

### Dimensions

|           |                    |
|-----------|--------------------|
| L         | 220mm NOM          |
| W         | 140mm NOM          |
| H         | 115mm NOM          |
| L1        | 250mm NOM          |
| L2        | 233mm NOM          |
| W1        | 100mm NOM          |
| W2        | 120mm NOM          |
| K         | 6.5mm NOM          |
| M (Earth) | Threaded Studs M10 |
| Lead      | Threaded Studs M10 |

### Packaging Specifications

|                          |         |
|--------------------------|---------|
| Packaging                | Bulk    |
| Packaging Quantity       | 1       |
| Typical Component Weight | 3,000 g |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.