



Click [here](#) for the 3D model.

General Information

Series	FM
Style	Radial Molded
Description	Radial Molded Double Layer Capacitor
RoHS	Yes
Lead	Wire Leads
AEC-Q200	No
Typical Component Weight	1.6 g
Miscellaneous	DischargeValue = 0.3 F.

Dimensions

W	10.5mm +/-0.5mm
H	11.5mm +/-0.5mm
T	6.5mm +/-0.5mm
S	5mm +/-0.5mm
LL	18mm +/-1mm
G	0.4mm +/-0.1mm
LT1	0.5mm +/-0.1mm
LT2	0.4mm +/-0.1mm

Packaging Specifications

Packaging	Ammo
Packaging Quantity	1000

Specifications

Capacitance	0.22 F
Tolerance	-20/+80%
Voltage DC	3.5 VDC
Temperature Range	-25/+70°C
Rated Temperature	70°C
ESR	100000 mOhms (1kHz)
Current (at 30 minutes after charging)	0.2 mAmps