


**General Information**

Series	L-RMQ
Style	SMD Multi-Layer
Core	Ferrite
RoHS	Yes

**Dimensions**

L	1mm +/-0.05mm
W	0.5mm +/-0.05mm
T	0.5mm +/-0.05mm

**Packaging Specifications**

Packaging	T&R
Packaging Quantity	10000

**Specifications**

Inductance	0.0082 uH (100 MHz)
Inductance Tolerance	5%
Inductance	8,200 pH
Rated Current	360 mAmps (MAX), 470 mAmps (Self Heating)
DC Resistance	270 mOhms
DC Resistance	0.27 Ohms
Quality Factor	46 at 800 MHz, 62 at 1500 MHz
Self-Resonant Frequency	3600 MHz MIN

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.