


L0603C1N0SRMST

Aliases (L0603C1N0SRMST)

Obsolete

KEMET, L-RMS, SMD Multi-Layer, 1000 pH, +/-0.3 nH, 0603



Click [here](#) for the 3D model.

Dimensions

Chip Size	0603
L	1.6mm +/-0.15mm
W	0.8mm +/-0.15mm
T	0.8mm +/-0.15mm
LL	0.3mm +/-0.2mm

Packaging Specifications

Packaging	T&R
Packaging Quantity	4000

General Information

Series	L-RMS
Style	Ferrite
Description	Surface Mount Inductor
RoHS	Yes
Core	Ceramic
Winding Type	Multilayer
Notes	Suggested Replacement - https://www.chilisin.com/en-global/Inductor/Product/BSCH_160808/BSCH001608081N0S00 .

Specifications

Inductance	1000 pH
Inductance Tolerance	+/-0.3 nH
Temperature Range	-40/+85°C
Current	300 mAmps (MAX)
DC Resistance	0.05 Ohms
Quality Factor	14 at 100 MHz, 40 at 500 MHz, 70 at 800 MHz, 90 at 1000 MHz
Self-Resonant Frequency	10000 MHz

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.