



General Information

Series	FW5
Description	Flex Suppressor High Permeability Type
Features	High Permeability Type
RoHS	Yes
Qualifications	UL94 HB, UL File No. E176124
Environment	RoHS Compliant, Halogen Free, PVC Free, Lead Free, Red Phosphorus Free

Specifications

Temperature Range	-40/+105°C
Permeability	250 μ At 3MHz
Effective Frequency	1 MHz to 3GHz
Specific Gravity	3.6 TYP
Thermal Conductivity	1.55 typical
Surface Resistivity	1 MOhm/sq. TYP

Dimensions

Sheet Size	240mmx50M
L	50000mm NOM
W	240mm NOM
T	0.05mm NOM

Packaging Specifications

Tape Thickness	0.01mm
Typical Component Weight	3803.69 g