

L0806C1R0MDMIT

Aliases (L0806C1R0MDMIT)

Obsolete

KEMET, L-DMI, Ferrite, 20%, 1,000 nH, 0806



Click [here](#) for the 3D model.

General Information

| | |
|-------------|----------------------------------|
| Series | L-DMI |
| Style | SMD Multi-Layer |
| Core | Ferrite |
| Description | Shielded, Surface Mount Inductor |
| RoHS | Yes |

Dimensions

| | |
|-----------|----------------|
| Chip Size | 0806 |
| L | 2mm +/-0.2mm |
| W | 1.6mm +/-0.2mm |
| T | 1mm MAX |

Packaging Specifications

| | |
|--------------------|------|
| Packaging | T&R |
| Packaging Quantity | 3000 |

Specifications

| | |
|----------------------|------------------|
| Inductance | 1 uH (1 MHz) |
| Inductance Tolerance | 20% |
| Rated Current | 1300 mAmps (MAX) |
| Temperature Range | -40/+85°C |
| Shielded | Yes |
| DC Resistance | 120 mOhms |
| DC Resistance | 0.12 Ohms (Max) |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.