



Click [here](#) for the 3D model.

General Information

Series	HP LDD Indust COG HT200C
Style	Radial
Description	Commercial, High Temperature
Features	LDD High Temperature 200C
RoHS	No
Prop 65	WARNING: Cancer and reproductive harm - https://www.p65warnings.ca.gov/
Termination	Nickel
AEC-Q200	No

Dimensions

L	5.08mm MAX
H	5.08mm MAX
T	2.54mm MAX
S	5.08mm +/-0.762mm
LL	3.175mm MIN
F	0.635mm +0.102/-0.051mm
G	1.65mm MAX

Specifications

Capacitance	0.01 uF
Tolerance	2%
Voltage DC	25 VDC
Temperature Range	-55/+200°C
Temp. Coefficient	COG

Packaging Specifications

Packaging	Waffle, Tray
-----------	--------------

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.