



General Information

Series	JSP
Dielectric	Metallized Polyester Stacked
Style	Radial
Features	DC Multipurpose Applications
RoHS	Yes
Termination	Tinned Wire
Lead	Wire Leads
AEC-Q200	No
Miscellaneous	This Part Number Has One Or More Features That Make It Nonstandard, Semi-Standard, Or Unusual Even Though It May Be A Catalog Part Number. Such Part Numbers Are Often Subject To Long Lead Times. Please Contact KEMET For Details. maxKO = 1890.

Dimensions

L	41.5mm +0.3mm
H	40mm +0.1mm
T	20mm +0.3mm
S	37.5mm +/-0.4mm
LL	4mm +2mm
F	1mm +/-0.05mm

Packaging Specifications

Packaging	Bulk, Bag
Packaging Quantity	126

Specifications

Capacitance	220 uF
Tolerance	10%
Voltage DC	63 VDC, 35.4 VDC (125C)
Voltage AC	40 VAC
Temperature Range	-55/+125°C
Rated Temperature	85°C
Dissipation Factor	1% 1kHz
Insulation Resistance	5.7 MOhms
Max dV/dt	15 V/us
Inductance	22 nH