



Click [here](#) for the 3D model.

#### Dimensions

Chip Size	0402
L	1mm +/-0.05mm
W	0.5mm +/-0.05mm
T	0.5mm +/-0.05mm

#### Packaging Specifications

Packaging	T&R
Packaging Quantity	10000

#### General Information

Series	L-RMS
Style	SMD Multi-Layer
Core	Ceramic
Description	Surface Mount Inductor
RoHS	Yes
Winding Type	Multilayer
Notes	Suggested Replacement - <a href="https://productfinder.pulseelectronics.com/part/BSCH0010050568NJCS">https://productfinder.pulseelectronics.com/part/BSCH0010050568NJCS</a> .

#### Specifications

Inductance	68 nH
Inductance Tolerance	5%
Temperature Range	-55/+125°C
Current	180 mAmps (MAX)
DC Resistance	1.2 Ohms
Quality Factor	11 at 100 MHz, 17 at 500 MHz, 18 at 800 MHz, 11 at 1000 MHz
Self-Resonant Frequency	750 MHz