



Click [here](#) for the 3D model.

#### General Information

|        |                                |
|--------|--------------------------------|
| Series | L-SWS                          |
| Style  | SMD Wire-Wound                 |
| Core   | Ferrite                        |
| RoHS   | Yes                            |
| Notes  | Last Order Date June 30, 2023. |

#### Dimensions

|           |                |
|-----------|----------------|
| Chip Size | 0806           |
| L         | 2mm +/-0.2mm   |
| W         | 1.6mm +/-0.2mm |
| T         | 1.6mm +/-0.2mm |

#### Packaging Specifications

|                    |      |
|--------------------|------|
| Packaging          | T&R  |
| Packaging Quantity | 2000 |

#### Specifications

|                         |                   |
|-------------------------|-------------------|
| Inductance              | 1.5 uH (7.96 MHz) |
| Inductance Tolerance    | 5%                |
| Rated Current           | 350 mAmps (MAX)   |
| Temperature Range       | -40/+105°C        |
| DC Resistance           | 470 mOhms         |
| DC Resistance           | 0.47 Ohms         |
| Self-Resonant Frequency | 135 MHz MIN       |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.