


LDEDD4100KA0N00

Aliases (DEDD4100KA0N00)

Obsolete

LDE, Film, Metallized PEN Stacked, Automotive Grade, 1 uF, 10%, 63 VDC, 40 VAC, 125°C, 2220, 4.4 mm



Click here for	or the	3D m	nodel.
----------------	--------	------	--------

General Information	
Series	LDE
Dielectric	Metallized PEN Stacked
Style	SMD Chip
Features	Automotive Grade
RoHS	Yes
Qualifications	AEC-Q200
AEC-Q200	Yes
Typical Component Weight	0.457 g
Shelf Life	104 Weeks
MSL	3

Dimensions	
Chip Size	2220
L	6mm +/-0.3mm
W	5mm +/-0.4mm
Т	4.4mm MAX
В	0.4mm +0.5/-0.3mm

Packaging Specifications	
Packaging	T&R
Packaging Quantity	1750

Specifications		
Capacitance	1uF	
Tolerance	10%	
Voltage DC	63 VDC	
Voltage AC	40 VAC	
Temperature Range	-55/+125°C	
Rated Temperature	125°C	
Dissipation Factor	0.8% 1kHz	
Insulation Resistance	400 MOhms	
Max dV/dt	100 V/us	

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 10/31/2025 © 2006 - 2025 YAGEO



LDEDD4100KA0N00


Aliases (DEDD4100KA0N00)


Obsolete


LDE, Film, Metallized PEN Stacked, Automotive Grade, 1 uF, 10%, 63 VDC, 40 VAC, 125°C, 2220, 4.4 mm


Simulations


For the complete simulation environment please visit Y-SIM.











Generated 10/31/2025 © 2006 - 2025 YAGEO

S11 Magnitude (db)



LDEDD4100KA0N00

Aliases (DEDD4100KA0N00)

LDE, Film, Metallized PEN Stacked, Automotive Grade, 1 uF, 10%, 63 VDC, 40 VAC, 125°C, 2220, 4.4 mm

These are simulations.

This is not a specification!

The responses shown represent the typical response for each part type. Specific responses may vary, depending on manufacturing variation affects of all parameters involved, including the specified tolerances applied to capacitance and unspecified variations of ESR, ESL, and leakage resistance.

The responses shown do not represent a specified or implied maximum capability of the device for all applications.

- The ESR used for ripple "Ripple Current/Voltage vs. Frequency" plots is the ESR at ambient temperature.

- The ESR used for ripple Ripple Currenty votage vs. rrequency plots is adjusted to each incremental temperature rise before the power and ripple current is calculated.
 The ESR in the "Temperature Rise vs. Ripple Current" plots is adjusted to each incremental temperature rise before the power and ripple current is calculated.
 The effects shown herein are based on measured data from a multiple part sample of the parts in question.
 Ripple capability of this device will be factored by thermal resistance (Rth) created by circuit traces (addi affects of all parameters involved, including the specified tolerances applied to capacitance and unspecified variations of ESR, ESL, and leakage resistance.
 The peak voltages generated in the "Temperature Rise vs. Combined Ripple Currents" plot are calculated for each frequency and are not combined with voltages
- generated at any other harmonics.

 Please consult with the catalog or field applications engineer for maximum capability of the device in specific applications.

All product information and data (collectively, the "Information") are subject to change without notice.

KEMET K-SIM is designed to simulate behavior of components with respect to frequency, ambient temperature, and DC bias levels. The responses shown represent the typical response for each part type. Specific responses may vary, depending on manufacturing variation effects of all parameters involved, including the specified tolerances applied to capacitance and unspecified variations of ESR, ESL, and leakage resistance.

All Information given herein is believed to be accurate and reliable, but is presented without guarantee, warranty, or responsibility of any kind, expressed or implied. Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

If you have any questions please contact K-SIM.

Generated 10/31/2025 © 2006 - 2025 YAGEO