



Click [here](#) for the 3D model.

General Information	
Series	MPLCG
Style	SMD Molded
Core	Metal Composite
Description	Shielded, Surface Mount Inductor
Features	Large Current Inductors
RoHS	Yes
Miscellaneous	40 (K) Temperature Rise Max.

Specifications	
Inductance	220 nH
Inductance Tolerance	20%
Temperature Range	-40/+125°C
Rated Temperature	120°C
Shielded	true
Current	10.2 A (Isat, 20% Drop In Inductance), 14.1 A (Irms, 40C Rise By Self Heating)
DC Resistance	2.7 mOhms

Dimensions	
Chip Size	0530(2120)
L	5.5mm MAX
W	5mm +/-0.2mm
T	3mm MAX
G	2.5mm +/-0.2mm

Packaging Specifications	
Typical Component Weight	350 mg
Packaging	T&R, 380mm
Packaging Quantity	3500

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.