


PEG124VG2220QE4

PEG124, Aluminum, Aluminum Electrolytic, 22 uF, -10/+30%, 400 VDC, -40/+105°C



Click [here](#) for the 3D model.

General Information

| | |
|--------------------------|--|
| Series | PEG124 |
| Dielectric | Aluminum Electrolytic |
| Style | Axial |
| Description | Long Life Axial Aluminum Electrolytic |
| RoHS | Yes |
| Lead | Wire Leads |
| AEC-Q200 | No |
| Halogen Free | Yes |
| Typical Component Weight | 11 g |
| Miscellaneous | Life Calculation Based On Maximum Ripple Current, Please Contact KEMET For More Information. |

Notes
L1 is KEMETs recommendation for minimum distance between symmetrical Lead bend. Available only for Customer specific part numbers. Lead bend dimensions must be specified and confirmed per article. Dimensions D And L Include Slewing.

Shelf Life 156 Weeks

Specifications

| | |
|-------------------|--|
| Capacitance | 22 uF |
| Tolerance | -10/+30% |
| Voltage DC | 400 VDC |
| Temperature Range | -40/+105°C |
| Rated Temperature | 105°C |
| Life | 15000 Hrs |
| ESR | 2700 mOhms (100Hz 20C), 1200 mOhms (100kHz 20C) |
| Ripple Current | 0.209 Amps (100Hz 105C), 1.4 Amps (5kHz 60C), 0.5 Amps (5kHz 105C) |
| Leakage Current | 26 uA (5min 20°C) |

Dimensions

| | |
|----|-----------------|
| D | 16mm +/-0.5mm |
| L | 37mm +/-1mm |
| L1 | 43mm MIN |
| LL | 42mm +3/-2mm |
| F | 0.8mm +/-0.03mm |

Packaging Specifications

| | |
|-----------|------|
| Slewing | Yes |
| Packaging | Tray |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.