



Click [here](#) for the 3D model.

Dimensions

Chip Size	1770(6868)
L	17mm +/-0.5mm
W	17.1mm +/-0.5mm
T	7mm MAX
G	11.9mm NOM

Packaging Specifications

Typical Component Weight	11 g
Packaging	T&R, 330mm
Packaging Quantity	100

General Information

Series	MPX
Style	SMD Molded
Core	Metal Composite
Description	Surface Mount Inductor
Features	Power Inductors
RoHS	Yes
Miscellaneous	40 (K) Temperature Rise Max.

Specifications

Inductance	4700 nH
Inductance Tolerance	20%
Temperature Range	-55/+155°C
Shielded	Yes
Current	23.5 A (Irms, 40C Rise By Self Heating), 24 A (Isat, 20% Drop In Inductance), 33.5 A (Isat, 30% Drop In Inductance)
DC Resistance	4.8 mOhms
Self-Resonant Frequency	10 MHz